

氟樹脂管

包裝：5m、20m

訂購代號：

SET 0640 - 20 - C - C



① 品名

② 配管徑 (外徑×內徑)：

編號	公制								英制			
	0420	0425	0640	0860	1075	1080	1290	1210	1613	1/4	3/8	1/2
外徑	φ4	φ4	φ6	φ8	φ10	φ10	φ12	φ12	φ16	φ6.35	φ9.53	φ12.7
內徑	φ2	φ2.5	φ4	φ6	φ7.5	φ8	φ9	φ10	φ13	φ4.57	φ6.99	φ9.56

③ 配管長度：

5：5m / 20：20m / 50：50m / 100：100m

④ 配管顏色：

C：透明色 / B：黑色 (僅限SET)

⑤ 無塵室規格：(無塵室規格管長限5, 20m)

C：無塵室規格 / 無記號：標準規格

規格：

使用流體	空氣、水、腐蝕性液體 (※)
最高使用壓力	0.7~2.7 MPa
使用溫度範圍	-65~+260°C (不凍結)


※1. 使用藥品時。
 ※2. 溫度上昇。
 ※3. 流體為液體時建議使用嵌入環。

聚醯胺管—SNT管 (標準型)

包裝：20m、100m

訂購代號：

SNT 0640 - 20 - W



① 品名

② 配管徑 (外徑×內徑)：

編號	0420	0425	0640	0860	1075	1080	1290	1210	1613
	外徑	φ4	φ4	φ6	φ8	φ10	φ10	φ12	φ12
內徑	φ2	φ2.5	φ4	φ6	φ7.5	φ8	φ9	φ10	φ13

③ 配管長度：

20：20m (SNT1613僅適20m) / 100：100m

④ 配管顏色：

W：半透明色

規格：

使用流體	空氣、水、飲料水體
最高使用壓力	1.5 MPa (20°C 65%RH時)
使用真空壓力	-100 kPa
使用溫度範圍	-15~+60°C (不凍結)

<p>SFT 氟樹脂管(PFA)-標準型 Fluororesin Tube</p> <p>型式</p> <table border="1"> <tr> <td>SFT0420-□-C</td> <td>SFT1290-□-C</td> <td>SFT0425-□-C</td> <td>SFT1613-□-C</td> </tr> <tr> <td>SFT0640-□-C</td> <td>SFT1/4-□-C</td> <td>SFT0860-□-C</td> <td>SFT3/8-□-C</td> </tr> <tr> <td>SFT1075-□-C</td> <td>SFT1/2-□-C</td> <td>SFT1080-□-C</td> <td></td> </tr> </table>	SFT0420-□-C	SFT1290-□-C	SFT0425-□-C	SFT1613-□-C	SFT0640-□-C	SFT1/4-□-C	SFT0860-□-C	SFT3/8-□-C	SFT1075-□-C	SFT1/2-□-C	SFT1080-□-C		<p>SFT CLEAN ROOM 氟樹脂管(PFA)-無塵室規格 Fluororesin Tube</p> <p>型式</p> <table border="1"> <tr> <td>SFT0420-□-C-C</td> <td>SFT1080-□-C-C</td> </tr> <tr> <td>SFT0425-□-C-C</td> <td>FT1290-□-C-C</td> </tr> <tr> <td>SFT0640-□-C-C</td> <td>SFT1/4-□-C-C</td> </tr> <tr> <td>SFT0860-□-C-C</td> <td>SFT3/8-□-C-C</td> </tr> <tr> <td>SFT1075-□-C-C</td> <td>SFT1/2-□-C-C</td> </tr> </table>	SFT0420-□-C-C	SFT1080-□-C-C	SFT0425-□-C-C	FT1290-□-C-C	SFT0640-□-C-C	SFT1/4-□-C-C	SFT0860-□-C-C	SFT3/8-□-C-C	SFT1075-□-C-C	SFT1/2-□-C-C
SFT0420-□-C	SFT1290-□-C	SFT0425-□-C	SFT1613-□-C																				
SFT0640-□-C	SFT1/4-□-C	SFT0860-□-C	SFT3/8-□-C																				
SFT1075-□-C	SFT1/2-□-C	SFT1080-□-C																					
SFT0420-□-C-C	SFT1080-□-C-C																						
SFT0425-□-C-C	FT1290-□-C-C																						
SFT0640-□-C-C	SFT1/4-□-C-C																						
SFT0860-□-C-C	SFT3/8-□-C-C																						
SFT1075-□-C-C	SFT1/2-□-C-C																						
<p>SET 氟樹脂管(FEP)-標準型 Fluororesin Tube</p> <p>型式</p> <table border="1"> <tr> <td>SET0420-□-C</td> <td>SET1290-□-C</td> <td>SET0425-□-C</td> <td>SET1210-□-C</td> </tr> <tr> <td>SET0640-□-C</td> <td>SET1613-□-C</td> <td>SET0860-□-C</td> <td>SFT1/4-□-C</td> </tr> <tr> <td>SET1075-□-C</td> <td>SET3/8-□-C</td> <td>SET1080-□-C</td> <td></td> </tr> </table>	SET0420-□-C	SET1290-□-C	SET0425-□-C	SET1210-□-C	SET0640-□-C	SET1613-□-C	SET0860-□-C	SFT1/4-□-C	SET1075-□-C	SET3/8-□-C	SET1080-□-C		<p>SET CLEAN ROOM 氟樹脂管(FEP)-無塵室規格 Fluororesin Tube</p> <p>型式</p> <table border="1"> <tr> <td>SET0420-□-C-C</td> <td>SET1290-□-C-C</td> </tr> <tr> <td>SET0425-□-C-C</td> <td>SET1210-□-C-C</td> </tr> <tr> <td>SET0640-□-C-C</td> <td>SFT1/4-□-C-C</td> </tr> <tr> <td>SET0860-□-C-C</td> <td>SFT3/8-□-C-C</td> </tr> <tr> <td>SET1075-□-C-C</td> <td>SFT1/2-□-C-C</td> </tr> </table>	SET0420-□-C-C	SET1290-□-C-C	SET0425-□-C-C	SET1210-□-C-C	SET0640-□-C-C	SFT1/4-□-C-C	SET0860-□-C-C	SFT3/8-□-C-C	SET1075-□-C-C	SFT1/2-□-C-C
SET0420-□-C	SET1290-□-C	SET0425-□-C	SET1210-□-C																				
SET0640-□-C	SET1613-□-C	SET0860-□-C	SFT1/4-□-C																				
SET1075-□-C	SET3/8-□-C	SET1080-□-C																					
SET0420-□-C-C	SET1290-□-C-C																						
SET0425-□-C-C	SET1210-□-C-C																						
SET0640-□-C-C	SFT1/4-□-C-C																						
SET0860-□-C-C	SFT3/8-□-C-C																						
SET1075-□-C-C	SFT1/2-□-C-C																						

<p>SNT 聚醯胺管 Polyamide Tube</p> <p>型式</p> <table border="1"> <tr> <td>SNT0420-□-W</td> <td>SNT1080-□-W</td> </tr> <tr> <td>SNT0425-□-W</td> <td>SNT1290-□-W</td> </tr> <tr> <td>SNT0640-□-W</td> <td>SNT1210-□-W</td> </tr> <tr> <td>SNT0860-□-W</td> <td>SNT1613-□-W</td> </tr> <tr> <td>SNT1075-□-W</td> <td></td> </tr> </table>	SNT0420-□-W	SNT1080-□-W	SNT0425-□-W	SNT1290-□-W	SNT0640-□-W	SNT1210-□-W	SNT0860-□-W	SNT1613-□-W	SNT1075-□-W	
SNT0420-□-W	SNT1080-□-W									
SNT0425-□-W	SNT1290-□-W									
SNT0640-□-W	SNT1210-□-W									
SNT0860-□-W	SNT1613-□-W									
SNT1075-□-W										